

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0347290200](#)
Status: **Active**
Overview: [Stac64 Single, Multi-Pocket and Hybrid Header System](#)
Description: [Stac64 Receptacle Housing, 20 Circuits, Dual Row, Polarization A, Black, Tray](#)

Documents:

| | |
|---|--|
| Drawing (PDF) | Application Specification AS-34729-020-001 (PDF) |
| 3D Model (PDF) | Packaging Specification PK-31301-201-001 (PDF) |
| 3D Model | Brochure (PDF) |
| Product Specification PS-34729-020-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification 347290200-AS-CH-000 (PDF) | |

General

| | |
|----------------|--|
| Product Family | Crimp Housings |
| Series | 34729 |
| Application | Automotive, Signal, Wire-to-Board |
| Overview | Stac64 Single, Multi-Pocket and Hybrid Header System |
| Polarization | A |
| Product Name | Stac64 |
| UPC | 884982006546 |

Physical

| | |
|-------------------------------|--------------------------------|
| Circuits (maximum) | 20 |
| Color - Resin | Black |
| Gender | Receptacle |
| Glow-Wire Capable | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 7.530/g |
| Number of Rows | 2 |
| Packaging Type | Tray |
| Panel Mount | N/A |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Polarized to Mating Part | Yes |
| Stackable | Yes |
| Temperature Range - Operating | -40° to +100°C |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 10.0A |
|-------------------------------|-------|

Solder Process Data

| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|---------------------------------------|
| Application Specification | 347290200-AS-CH-000, AS-34729-020-001 |
| Packaging Specification | PK-31301-201-001 |
| Product Specification | PS-34729-020-001 |
| Sales Drawing | SD-34729-020-001 |



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34729](#) Series

Mates With

[34690](#) 2.54mm Pitch Stac64 Vertical Header, [34691](#) 2.54mm Pitch Stac64 Right Angle Header

Use With

[34803](#) CTX64 Female Terminal

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34729-0200](#)