

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395126019

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

3.81mm Pitch Eurostyle Horizontal PCB Header, Green Housing, 19 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-39500-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39512

N/A

PCB Header

Eurostyle Terminal Blocks

ESE, Eurostyle Pluggable

Euro Block

822350463966

Physical

Circuits (Loaded)

Entry Angle

Lock to Mating Part

Number of Rows

Orientation

PC Tail Length

PCB Thickness - Recommended

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Shrouded

Stackable

Temperature Range - Operating

Wire Size AWG

19

N/A

None

1

Horizontal

3.50mm

2.50mm

No

3.81mm

3.81mm

Yes

Fully

No

-40° to +105°C

N/A

Electrical

Current - Maximum per Contact

Voltage - Maximum

8.0A

300V

Material Info


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-39500-001-001

SD-39501-002, SD-39512-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Not Relevant

Not Relevant

Not Reviewed

Search Parts in this Series

39512 Series

Mates With

Most 3.81mm Pitch Industry Standard Plugs, 39513 Vertical Plug, 39510 Horizontal Plug

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39512-6019](#)