

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0414224001](#)  
**Status:** **Active**  
**Description:** 250 Spade Term LIF O/Lock

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Crimp Terminals  
 Series [41422](#)  
 Crimp Quality Equipment Yes  
 UPC 800753811874

**Physical**

Net Weight 1.983/g

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing SD-41422-4X-001, SD-41422-4X-002,  
 SD-41422-4X-003

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2021)4569-DC (8  
 July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[41422 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Mini-Mac Applicator, [638821000](#)

10-13 AWG Wire

Mini-Mac Applicator, [638821200](#)

Double Crimp

Applicator for 14-18

AWG Wire

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[41422-4001](#)