

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0511103051](#)  
**Status:** **Active**  
**Overview:** [Milli-Grid Connector System](#)  
**Description:** 2.00mm Pitch, Milli-Grid Receptacle Housing, 30 Circuits, with Center Polarization Key, with Locking Ramp, Lead-Free

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 503940001-AS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-51110-300-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">Product Specification PS-51110-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**Application tooling part link**

Application Tooling Part Link	63824-2800
-------------------------------	------------

**General**

Product Family	Crimp Housings
Series	<a href="#">51110</a>
Application	Signal, Wire-to-Board
Comments	Applicable Wire Ranges: 24-30 AWG (series <a href="#">50394</a> terminal) and 22-28 AWG (series <a href="#">87396</a> terminal)
Overview	<a href="#">Milli-Grid Connector System</a>
Product Name	Milli-Grid
UPC	800753630512

**Physical**

Circuits (maximum)	30
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	0.649/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	503940001-AS-000
Packaging Specification	PK-51110-300-001
Product Specification	PS-51110-001-001
Sales Drawing	SD-51110-XX5X-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[51110 Series](#)

**Mates With**

Milli-Grid Headers [87758](#) , [87759](#) , [87760](#) , [87831](#) , [87832](#) <br>Milli-Grid BMI Header [151013](#) <br>Milli-Grid Low-Halogen Headers [151117](#) , [151118](#) , [151119](#) , [151120](#)

**Use With**

Milli-Grid Crimp Terminals [50394](#) , [87396](#) <br>Milli-Grid Pre-Crimped Leads [797581095](#) , [797581096](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extractor Tool  
for Milli-Grid 2.0  
Housings

638242800

This document was generated on 02/02/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[51110-3051](#)