

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0847000001](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Receptacle, Inline, Industrial, 8/8

Documents:

[3D Model](#) [Drawing \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Industrial Receptacles
 Series [84700](#)
 IP Rating IP67
 Overview [Brad Industrial Ethernet Solutions](#)
 Product Name RJ45
 Type PCB Mount
 UPC 756054460405

Physical

Coupling Type External Thread
 Gender Male
 Keyway None
 Length N/A
 Material - Component PBT
 Mounting Thread Size 1" - 14 UNC
 Net Weight 22.670/g
 Orientation Straight
 Panel Mount Front
 Poles N/A
 Temperature Range - Operating -20° to +80°C
 Wire Size AWG N/A
 Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 1.5A
 Voltage - Maximum 125V

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Sales Drawing SD-84700-007-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)4578-DC (25
 June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000380967_00_000.pdf

Search Parts in this Series

[84700 Series](#)

Mates With

[847000002 Plug](#), [84702 Cable Assemblies](#)

Use With

[847000003 Dust Cover](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84700-0001](#)