

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0847330008

Status:

Active

Overview:

Sealed Industrial USB Solutions

Description:

Sealed Industrial USB 3.0 Type A Receptacle-to-USB Type A Plug Dual-Ended Cordset, 5.00m Length



Documents:

Drawing (PDF)

Product Specification PS-84733-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	84733
Assembly Configuration	Dual Ended Connectors
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type A-to-A
Overview	Sealed Industrial USB Solutions
Product Name	Industrial USB
UPC	887191635545
Physical	
Cable Length	5.0m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Male
Material - Resin	PVC
Number of Rows	2
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Size AWG	N/A
Wire/Cable Type	USB
Electrical	
Current - Maximum per Contact	1.0A
Impedance	Non-constant
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-84733-001-001
Sales Drawing	SD-84733-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

84733 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84733-0008](#)