

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010019](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Stamped Crimp Contact for 10A Inserts and Modules, Female, Gold (Au) Plated Phosphor Bronze, 0.75-2.50mm² (18-14 AWG), 2000 per Reel



Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Contact Type	Stamped Crimp
Exclude SD Check	Yes
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Contacts
Product Name	GWconnect
UPC	887191864778

Physical

Gender	Female
Material - Contact	Phosphor Bronze
Material - Plating	Gold
Net Weight	0.400/g
Number of Grooves	0
Packaging Type	Reel
Stripping Length	3.20mm
Wire Size AWG	14-18
Wire Size mm ²	0.75-2.50

Electrical

Current - Maximum per Contact	10.0A
-------------------------------	-------

Material Info

Engineering Number	7100.4039.1
--------------------	-------------

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601](#) Series

Mates With

[93601](#) Male Stamped Crimp Contact

Use With

S-D, S-K, S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0019](#)