

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936014748](#)
Status: **Active**
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: GWconnect RJ45 Wire Plug Assembly, Size 3A «21x21», Side Entry, 8p/4C Plug, M20 Plastic Gland and Hood, with 2 Red Polarizing Keys, Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Color - Cable Jacket	N/A
Component Size	3A «21x21»
Component Type	Wire Plug Assembly
IP Rating	IP66, IP67
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Modular Plugs / Jacks
Product Name	GWconnect®
Type	RJ45
UPC	887191846903

Physical

Entry Location	Side
Flammability	UL 94V-0
Gland Color	Light Grey RAL 7035
Hood Color	Grey RAL 7035
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Hood	Polyamide
Material - Nut	Polyamide
Material - Plating	Gold
Material - Plug	PBT
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8p/4C
Temperature Range - Operating	-40°C to +120°C
Thread Size	M20
Thread Type	(M) Metric

Material Info

Engineering Number	7940.3412.0
--------------------	-------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-4748](#)