

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936014761](#)  
**Status:** **Active**  
**Overview:** GWconnect® Heavy Duty Connectors (HDC)  
**Description:** GWconnect RJ45 Wire Plug Assembly, Size 3A «21x21», Side Entry, 8p/4C Plug PROFINET, M20 Metal Gland and Hood, with 2 Red Polarizing Keys, Black

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Color - Cable Jacket	N/A
Comments	PROFINET
Component Size	3A «21x21»
Component Type	Wire Plug Assembly
IP Rating	IP66, IP67
Overview	<a href="#">GWconnect® Heavy Duty Connectors (HDC)</a>
Product Category	Modular Plugs / Jacks
Product Name	GWconnect®
Type	RJ45
UPC	887191847955

**Physical**

Entry Location	Side
Flammability	UL 94V-0
Hood Coating	Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Stainless Steel
Material - Gasket	NBR
Material - Hood	Die-cast Aluminum
Material - Nut	Stainless Steel
Material - Plating	Gold
Material - Plug	PBT
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8p/4C
Temperature Range - Operating	-40°C to +120°C
Thread Size	M20
Thread Type	(M) Metric

**Material Info**

Engineering Number	7940.3486.1
--------------------	-------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[93601](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-4761](#)