

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936014811](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect RJ45 Wire Plug Assembly, Size 3A «21x21», Top Entry, 8p/8C + 2pC Plug, Pg11 Plastic Gland and Hood, with 2 Red Polarizing Keys, Black

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Color - Cable Jacket	N/A
Component Size	3A «21x21»
Component Type	Wire Plug Assembly
IP Rating	IP66, IP67
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Modular Plugs / Jacks
Product Name	GWconnect
Type	RJ45
UPC	887191851471

**Physical**

Entry Location	Top
Flammability	UL 94V-0
Gland Color	Black RAL 9005
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Hood	Polyamide
Material - Nut	Polyamide
Material - Plating	Gold
Material - Plug	PBT
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8p/8C + 2pC
Temperature Range - Operating	-40° to +120°C
Thread Size	Pg11
Thread Type	(Pg)

**Material Info**

Engineering Number	7982.3310.1
--------------------	-------------



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[93601 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-4811](#)