

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **5025781100**
Status: **Active**
Overview: CLIK-Mate Wire-to-Board Connectors
Description: 1.50mm Pitch, CLIK-Mate Plug Crimp Housing, Single Row, Positive Lock, 11 Circuits, Beige

Documents:

3D Model	Product Specification 5025781000-PS-000 (PDF)
3D Model (PDF)	Product Specification 5025781002-PS-000 (PDF)
Drawing (PDF)	Product Specification 5025781003-PS-000 (PDF)
Product Specification 5025780000-PS-000 (PDF)	Product Specification 5025781004-PS-000 (PDF)
Product Specification 5025780001-PS-000 (PDF)	Application Specification AS-502578-001-001 (PDF)
Product Specification 5025780002-PS-000 (PDF)	Application Specification AS-503395-001-001 (PDF)
Product Specification 5025780003-PS-000 (PDF)	Packaging Specification SPK-502578-001-001 (PDF)
Product Specification 5025780004-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series [502578](#)
Application Signal, Wire-to-Board
Overview [CLIK-Mate Wire-to-Board Connectors](#)
Product Name CLIK-Mate
UPC 800756700823


Physical

Circuits (maximum) 11
Color - Resin Beige
Flammability SC-0
Gender Plug
Glow-Wire Capable No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin PBT
Net Weight 503.400/mg
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 1.50mm
Pitch - Termination Interface 1.50mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification AS-502578-001-001, AS-503395-001-001
Packaging Specification SPK-502578-001-001
Product Specification 5025780000-PS-000, 5025780001-PS-000, 5025780002-PS-000, 5025780003-PS-000, 5025780004-PS-000, 5025781000-PS-000, 5025781002-PS-000, 5025781003-PS-000, 5025781004-PS-000
Sales Drawing 5025780000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[502578](#) Series

Mates With

CLIK-Mate Bottom-Entry Receptacle [503395](#)
. CLIK-Mate Right Angle Receptacles
[503175](#) , [502585](#) , [213226](#) . CLIK-Mate
Vertical Receptacles [503159](#) , [502584](#) ,
[213225](#)

Use With

CLIK-Mate Tin Terminals [502579](#) , [503429](#)

 CLIK-Mate Gold Terminals [213028](#) ,
[213029](#)
 CLIK-Mate Pre-Crimped Lead
[797581011](#) , [215710](#) , [215711](#)

This document was generated on 12/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[502578-1100](#)