

BU-P1581-@
(Panel Mount Banana Jack)



- Mueller's BU-P1581 is a Banana Jack that mounts into panels ranging in thickness from 0.063" (1.6mm) to 0.375" (9.5mm).
 - Pole Threads: ¼-20
- Material:
 - Body – Nickel plated Brass
 - Insulator – Polycarbonate
 - Lock Washer – Nickel plated Steel
 - Hex Nut – Nickel plated Brass
- Ratings:
 - Operating Temperature: 115°C (239°F)
 - For personal safety, do not hold when voltages exceed 30 Vrms/60 Vdc.
 - Hands free use up to 2500 WVDC
 - Current – 15 Amps
- Color: The "@" in the model number represents color. Available colors:
 - 0 Black, -2 Red,
- RoHS 3 Compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-P1581-0](#) [BU-P1581-2](#)