

BU-46X

(Mini Plier Style Stainless Steel Clip without Insulators)



- Overall Length of 2.9" (74mm), Width of 0.5" (13mm), Height of 2" (51mm)
- Maximum Jaw opening of 1.13" (29mm).
- Connection: Solder or Crimp
- Material:
 - Clip – 304 Stainless Steel
- Rating: 50 Amps
- Can be used with BU-46PR-@ Insulators (Sold Separately)
- RoHS Compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-46X](#)