


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	MINIMUM LENGTH	WEIGHT	FERRULE TYPE
F9D4-NM1	39.37 in. [1 meter]	.50lb./10 pcs. (230.4g/10 pcs.)	ZIRCONIA
F9D4-NM2	78.74 in. [2 meters]	.82 lb./10 pcs. (327.8g/10 pcs.)	ZIRCONIA
F9D4-NM3	118.11 in. [3 meters]	1.13 lb./10 pcs. (515.2g/10 pcs.)	ZIRCONIA
F9D4-NM10	393.7 in. [10 meters]	3.32 lb./10 pcs. (1512.0g/10 pcs.)	ZIRCONIA

3mm YELLOW JACKETED
RISER RATED DUPLEX
FIBER OPTIC CABLE



NOTES:

1. SEE CURRENT CATALOG FOR PACKAGE QUANTITY.
2. DUPLEX 3mm JACKETED SINGLEMODE, 9/125μm GLASS OPTICAL FIBER, RISER RATED.
3. TERMINATED WITH FC CONNECTORS. ASSEMBLED WITH TEMPERATURE CURED EPOXY.
4. CABLE JACKET COLOR IS YELLOW. BOOT COLOR IS BLUE.
5. MINIMUM INSERTION LOSS PER CONNECTOR: .35dB PER FOTP-171.
6. MINIMUM RETURN LOSS PER CONNECTOR: 40dB OR GREATER FOR SPC POLISH.
7. DUST CAPS MAY VARY FROM ONES SHOWN.
8. ALL DIMENSIONS IN BRACKETS ARE METRIC.

CAD FILENAME/LAYERS		M01010CM_DC_00A.PRT	
<h1>PANDUIT</h1> CORP. TINLEY PARK, ILLINOIS			
DUPLEX SINGLEMODE FIBER OPTIC FC PIGTAIL (F9D4-NM SERIES) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
(.X) ±		(.XXX) ±	
(.XX) ±		ANGLES ±	
DRAWN BY	MAT'L:	SCALE	NONE
EFK			
DATE	SEE NOTES	DRAWING NO.	DWG
01-14-01		01010-37	A
CHK'D			SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	01-14-01	EFK		RELEASED FOR PRODUCTION	01010-37			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[F5D4-NM2Y](#)