


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	MINIMUM LENGTH	WEIGHT	FERRULE TYPE
F9D4-4M1	39.37 in. [ 1 meter ]	.70 lb./10 pcs. [ 318.4g/10 pcs. ]	ZIRCONIA
F9D4-4M2	78.74 in. [ 2 meters ]	1.01 lb./10 pcs. [ 460.8g/10 pcs. ]	ZIRCONIA
F9D4-4M3	118.11 in. [ 3 meters ]	1.32 lb./10 pcs. [ 603.2g/10 pcs. ]	ZIRCONIA
F9D4-4M6	236.2 in. [ 6 meters ]	2.26 lb./10 pcs. [ 1030.4g/10 pcs. ]	ZIRCONIA
F9D4-4M9	354.3 in. [ 9 meters ]	3.20 lb./10 pcs. [ 1457.6g/10 pcs. ]	ZIRCONIA
F9D4-4M10	393.7 in. [ 10 meters ]	3.52 lb./10 pcs. [ 1600.0g/10 pcs. ]	ZIRCONIA
F9D4-4M12	472.4 in. [ 12 meters ]	4.14 lb./10 pcs. [ 1884.8g/10 pcs. ]	ZIRCONIA
F9D4-4M15	590.5 in. [ 15 meters ]	5.08 lb./10 pcs. [ 2312.0g/10 pcs. ]	ZIRCONIA

3mm YELLOW JACKETED RISER RATED DUPLEX FIBER OPTIC CABLE

PRINTED CABLE



**NOTES:**

1. SEE CURRENT CATALOG FOR PACKAGE QUANTITY.
2. DUPLEX 3mm JACKETED SINGLEMODE, 9/125µm GLASS OPTICAL FIBER, RISER RATED.
3. TERMINATED WITH FC CONNECTORS. ASSEMBLED WITH TEMPERATURE CURED EPOXY.
4. CABLE JACKET COLOR IS YELLOW. BOOT COLOR IS BLUE.
5. MINIMUM INSERTION LOSS PER CONNECTOR: .35dB PER FOTP-171.
6. MINIMUM RETURN LOSS PER CONNECTOR: 40dB OR GREATER FOR SPC POLISH.
7. DUST CAPS MAY VARY FROM ONES SHOWN.
8. ALL DIMENSIONS IN BRACKETS ARE METRIC.

CDD FILENAME/LAYERS		M01010CN_DC_00A.PRT	
<b>PANDUIT</b> CORP. TINLEY PARK, ILLINOIS			
DUPLX SINGLEMODE FIBER OPTIC PATCHCORDS FC TO FC CONFIGURATION (F9D4-4M SERIES) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±            (.XXX) ± (.XX) ±            ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY EFK	MAT'L:	SCALE NONE	
DATE 01-14-01	SEE NOTES	DRAWING NO. 01010-38	DWG A SIZE
CHK'D			

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	01-14-01	EFK		RELEASED FOR PRODUCTION	01010-38				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[F5S4-4M1Y](#)