






.17 LB/10 PCS (78 g/10 PCS)

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



3/8-32 UNEF THREADS
(2 PLCS.)



PART NUMBER		CMF***	
TITLE			
MINI-COM 3GHz F-TYPE COUPLER MODULE			
CUSTOMER DRAWING			
ITEM REVISION NAME			
M01557AA/01			
DATASET FILE NAME		MATERIAL : MODULE BASE: ABS COUPLER: NICKEL PLATED BRASS	
M01557AA_DC04/01A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [.3] .XX ± .03 [.8] ANGLES ±		DRAWING NUMBER: 01557-04	
 THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
JSP	3-16-04	JCO	NONE
SHT 1 OF 1			SIZE
			A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CMFBL](#) [CMFIW](#) [CMFWH](#)