



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	WEIGHT
NKA6XPPG48Y	2.36 lb (1070.48 g)

- NOTES:
- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
 - MATERIAL:
 PANEL HOUSING: STEEL
 RJ45 MODULES: THERMOPLASTIC RESIN UL94V-0
 PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
 BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
 RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
 - 48 PORT ANGLED PATCH PANEL 8 POSITION 8 WIRE.
 - THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
 - FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) M6x1x15MM METRIC SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
 - DIMENSIONS IN BRACKETS ARE IN METRIC.
 - USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
 - RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.



PART NUMBER	SEE CHART	PRODUCT SPEC/PKG SPEC	N/A
I.I. NUMBER	N/A	WORK INSTRUCTION	N/A
TITLE			
NETKEY CAT6A 48 PORT ANGLED PATCH PANEL			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02088AP/00	
DATASET FILE NAME		M02088AP_DC45/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .1 [2.54] .xxx ± .005 [0.127]		SEE NOTE 2	
.xx ± .01 [0.25] ANGLES ± 5°		DRAWING NUMBER:	
		02088-45	
DRAWN BY	DATE	CHK	SCALE
BJN	2-4-15	MDJR	.25:1
SHT 1 OF 1			SIZE
A			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	2-5-15	BJN	MDJR	LPH	RELEASED TO PRODUCTION	02088-45

D10100DA/14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[NKA6XPPG48Y](#)