


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	"A" MIN.	"B"	"C"	"D"	MATERIAL	COLOR
T038X000YP1	100 [30.5]	1.000 [25.4]	0.3125 [7.94]	0.375 [9.5]	GMY4-HT	WHITE
T050X000YP1	100 [30.5]	1.000 [25.4]	0.25 [6.35]	0.5 [12.5]	GMY4-HT	WHITE
T038X000Y01	100 [30.5]	1.000 [25.4]	0.3125 [7.94]	0.375 [9.5]	GMY4-HT	BLACK
T050X000Y01	100 [30.5]	1.000 [25.4]	0.25 [6.35]	0.5 [12.5]	GMY4-HT	BLACK



- NOTES:
 1. RIBBON RESIN RECOMMENDED
 2. [] DENOTE METRIC DIMENSIONS

D10100DA/12

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	10/09/13	PMNG	SEWH	MSAD	ADDED BLACK SUPER TACK OF 3/8 AND 1/2	GAECN01277
1	4/23/13	MIFT			ADDED 3/8 INCH TAPE INFORMATION	00822
0	5/16/12	JHAC			DRAWING RELEASE	6785

TITLE 3/8 INCH AND 1/2 INCH SUPER-TACK POLYESTER TAPES CUSTOMER DRAWING	
ITEM REVISION NAME 121043AA/03	PANDUIT TM
DATASET FILE NAME 121043AA/03_C10989/03	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
.x ± .15 [3.81] .xxx ± .064 [.163]	DRAWING NUMBER: C10989
.xx ± .1 [2.54] ANGLES ± 5 °	
THIRD ANGLE PROJECTION	
DRAWN BY JHAC	DATE 5/16/12
CHK	SCALE NTS
SHT 1 OF 1	
SIZE A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[T050X000YP1](#) [T050X000Y01](#)