






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

**NOTES:****1. SPLICE CAPACITY:**

- A. FOR (1) FWMHSS-3456: 24 SPLICE TRAYS  
3456 RIBBON FIBERS - 12 RIBBON SPLICES PER TRAY  
1152 INDIVIDUAL FIBERS - 48 SINGLE FIBER SPLICES PER TRAY

**2. DIMENSIONS IN [ ] ARE METRIC.****3. DOORS HAVE TOOLLESS REMOVAL AND OPEN TO 180°.****4. WEIGHT: 144 lbs (66 kg)****TABLE 1**

PART NUMBER	COLOR
FWMHSSBS-3456	BLACK
FWMHSSWS-3456	WHITE
FWMHSSGS-3456	GRAY

**TITLE**

HD FUSION 3456 FIBER WALL MOUNT HYPERSCALE  
SPLICE ENCLOSURE - SPLIT DOORS

**CUSTOMER DRAWING****ITEM REVISION NAME**

00174EXC/01

**DATASET FILE NAME**

00174EXC\_DC/01A


UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ±

.XXX ± .010 [0.3]

.XX ± .03 [0.8]

ANGLES ±



THIRD ANGLE  
PROJECTION

**PART NO.**

SEE TABLE 1

**DRAWING NUMBER:**

00174EXC-DC

**DRAWN BY**

SAT

**DATE**

10-10-19

**CHK**

ACBR

**SCALE**

NONE

**ECN**

00174EXC-DC

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10-21-19	SAT	ACBR	AW	INITIAL RELEASE	00174EXC-DC

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[FWMHSSBS-3456](#) [FWMHSSWS-3456](#)