

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

SE 12 PS - 4C R O

COLOR:
O = WEATHER
RESISTANT
BLACK

REEL

LENGTH:

L = 50' (15.2M)
LQ = 75' (22.9M)
C = 100' (30.5M)
CL = 150' (45.7M)
T = 200' (61.0M)
4C = 400' (121.9M)


MATERIAL:

PSFR = POLYETHYLENE TEREPHTHALATE
(FLAME RETARDANT PET)
PS = POLYETHYLENE TEREPHTHALATE
(PET)



NOMINAL DIAMETER:

12 = 0.125 (3.2)
25 = 0.250 (6.4)
38 = 0.375 (9.5)
50 = 0.500 (12.7)
75 = 0.750 (19.1)
100 = 1.000 (25.4)
125 = 1.250 (31.8)
150 = 1.500 (38.1)
200 = 2.000 (50.8)



SLEEVING
EXPANDABLE



NOTES:

1. ALL STRANDS OF THE PET SLEEVING SHALL BE THE SAME COLOR.
2. THE FLAME RETARDANT PET SHALL HAVE A WHITE TRACER.
3. REELS MAY HAVE SPLICES DEPENDING ON LENGTH (SEE CHART BELOW).
4. SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION CONCERNING PACKAGE SIZE, PART MATERIAL AND PART COLOR.



LENGTH	50 FT	75 FT	100 FT	150 FT	200 FT	400 FT
MAX SPLICES	1	1	1	2	2	4
MAX SPLICE DISTANCE (FT)	15	20	20	25	25	25

					TITLE							
					PAN-WRAP BRAIDED SLEEVING							
					CUSTOMER DRAWING							
					ITEM REVISION NAME							
					14B208BB/02							
					DATASET FILE NAME							
					14B208BB_DC_PAN-WRAP/02A							
					UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]							
					.x ± N/A .xxx ± N/A .xx ± N/A ANGLES ± N/A							
					THIRD ANGLE PROJECTION							
					MATERIAL:							
					SEE PART NUMBER DESCRIPTION							
					DRAWING NUMBER:							
					14B208BB_DC							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
02	07.27.20	BDK	DAEI	TGS	△ ADDED NOMINAL DIAMETERS 38, 125 AND 200 △ REMOVED NOTE "SE200P ONLY OFFERED IN THE STD PET MATERIALS" △ 50 FT WAS 20 FT △ ADDED NOTE 4 AND REMOVED PACKAGE SIZE FROM PANDUIT PART NUMBERS IN CHART	GAECN084695	DJSJ	7-8-14	VJS	N.T.S.		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[SE125PS-LQR0](#) [SE125PSFR-LQR0](#) [SE38PS-CLR0](#) [SE38PSFR-CLR0](#)