



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	NOMINAL I.D.	NO. OF CARRIERS	NO. OF STRANDS PER CARRIER	WEIGHT/100' lbs. (kg)
SE12TC-C	0.125 (3.18)	24	5	1.30 (0.59)
SE25TC-C	0.250 (6.35)	24	16	2.20 (1.00)
SE38TC-C	0.375 (9.53)	48	8	3.30 (1.50)
SE50TC-L	0.500 (12.70)	48	11	3.50 (1.59)
SE88TC-L	0.875 (22.23)	48	7	10.30 (4.67)
SE100TC-L	1.00 (25.40)	48	8	13.15 (5.96)
SE125TC-L	1.250 (31.75)	48	10	16.50 (7.48)
SE150TC-L	1.500 (38.10)	48	12	18.40 (8.35)
SE200TC-L	2.000 (50.80)	48	14	22.70 (10.30)



NOTES:

1. ALL STRANDS OF THE TC SLEEVING SHALL BE THE SAME COLOR.

2. REELS MAY HAVE SPLICES, DEPENDING ON LENGTH:

LENGTH	50 FT	100 FT	200 FT	500 FT	1000 FT
MAX SPLICES	0	1	1	2	3

3. CONFORMS TO MIL-SPEC AA-59569

TITLE					
TINNED COPPER BRAIDED SLEEVING					
CUSTOMER DRAWING					
ITEM REVISION NAME					
02345EBC/01					
DATASET FILE NAME					
02345EBC-DC/01A				MATERIAL:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				SEE PART NUMBER DESCRIPTION	
.X ± .XX ± 				DRAWING NUMBER:	
THIRD ANGLE PROJECTION				02345EBC-DC	
DRAWN BY	DATE	CHK	SCALE	SIZE	
JHNU	6/29/21		N/A	A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01	9/30/21	JHNU	DJW	JADE	REMOVED BUNDLE DIA. COLUMN	02345EBC-DC
00	6/29/21	JHNU	DJW	JADE	DRAWING RELEASED	02345EBC-DC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[SE12TC-C](#) [SE200TC-L](#) [SE38TC-C](#) [SE50TC-L](#) [SE150TC-L](#) [SE125TC-L](#) [SE25TC-C](#) [SE88TC-L](#) [SE100TC-L](#)