


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART No.	SIZE	WALL THICKNESS MAX	"A" LENGTH	"B" (ID)	LBS /100'
FT38-C	3/8"	.025"	100'	.375"	1.86
FT50-C	1/2"	.025"	100'	.500"	2.55
FT62-C	5/8"	.025"	100'	.625"	3.0
FT75-C	3/4"	.025"	100'	.750"	3.45
FT100-C	1"	.025"	100'	1.00"	4.5
FT125-C	1-1/4"	.025"	100'	1.25"	5.4
FT150-C	1-1/2"	.025"	100'	1.50"	6.2
FT200-L	2"	.025"	50'	2.00"	8.7
FT300-L	3"	.025"	50'	3.00"	19.0

NOTES:
 1) THIS PRODUCT IS A NON-EXPANDABLE
 PLEASE MEASURE YOUR APPLICATION DIAMETER.
 2) LENGTHS MAY NOT BE CONTINUOUS.



REFLECTIVE ALUMINUMIZED SURFACE BONDED TO HIGH-TEMP RESISTANT FIBERGLASS TUBE. REFLECTS RADIANT HEAT AWAY FROM DELICATE COMPONENTS. EASY SLIP ON INSTALLATION. CUTS WITH SCISSORS. AVAILABLE IN SILVER.

PRODUCT SPEC 1004937	PACKAGING SPEC 01025EBB
PART NUMBER SEE TABLE	WORK INSTRUCTION N/A
INSPECTION INSTRUCTION NUMBER 01025EBA-DS	FMEA & CONTROL PLAN NUMBER CP-878

TITLE FIBERGLASS INSULATING TUBING	
CUSTOMER DRAWING	
ITEM REVISION NAME 01025EBB/00	PANDUIT
DATASET FILE NAME 01025EBB/00	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
.X ±	.XXX ±
.XX ±	ANGLES ±
	THIRD ANGLE PROJECTION
MATERIAL: ALUMINUM LAMINATED FIBERGLASS (SILVER COLOR)	
DRAWING NUMBER: 01025EBB_DC	

01	7/20/21	BWG	MRJS	JADE	DRAWING RELEASED.	101537/00
----	---------	-----	------	------	-------------------	-----------

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							BWG	3/12/21	JADE	NONE		A

D10100DA/20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[FT300-L](#) [FT50-C](#) [FT100-C](#) [FT62-C](#) [FT75-C](#) [FT125-C](#) [FT150-C](#) [FT200-L](#) [FT38-C](#)