


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER **	PANEL THICKNESS	A ±TOL.	B ±0.015 (0.38)	C ±0.015 (0.38)	D +0.020 (0.51) -0.015 (0.38)	E REF.	F * ±TOL.	G * REF
GE_36F-C	0.026 - 0.036 (0.66 - 0.91)	0.025 ±0.010 (0.64 ±0.25)	0.045 (1.14)	0.087 (2.21)	0.030 (0.76)	0.106 (2.69)	0.060 (1.52) +0.005 (0.13) -0.025 (0.64)	0.150 (3.81)
GE_62F-C	0.036 - 0.062 (0.91 - 1.57)	0.035 ±0.013 (0.89 ±0.33)	0.070 (1.78)	0.130 (3.30)	0.030 (0.76)	0.131 (3.33)	0.105 (2.67) +0.005 (0.13) -0.025 (0.64)	0.150 (3.81)
GE_99F-C	0.062 - 0.099 (1.57 - 2.51)	0.054 ±0.013 (1.37 ±0.33)	0.108 (2.74)	0.155 (3.94)	0.030 (0.76)	0.169 (4.29)	0.125 (3.18) +0.005 (0.13) -0.025 (0.64)	0.150 (3.81)
GE_144F-C	0.099 - 0.144 (2.51 - 3.66)	0.090 ±0.013 (2.29 ±0.33)	0.152 (3.86)	0.192 (4.88)	0.030 (0.76)	0.213 (5.41)	0.160 (4.06) +0.005 (0.13) -0.035 (0.89)	0.150 (3.81)
GE_189F-C	0.144 - 0.189 (3.66 - 4.80)	0.125 ±0.010 (3.20 ±0.25)	0.206 (5.23)	0.255 (6.48)	0.046 (1.17)	0.297 (7.55)	0.240 (6.09) +0.005 (0.13) -0.035 (0.89)	0.150 (3.81)

NOTES:

- * 1) DIM'S F & G APPLY ONLY TO SLOTTED GROMMET EDGING.
- ** 2) PART NO. EXAMPLE:
- GE S 36 F - C 0
 WEATHER RESISTANT BLACK
 F=POLYETHYLENE
 MAX. PANEL THICKNESS
 S=SOLID
 E=SLOTTED
 GROMMET EDGING
- 3) SEE CURRENT PRICE SHEET FOR PART NO. SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 4) COLOR: a) NATURAL
 b) -0 AFTER PART NO. DENOTES WEATHER RESISTANT BLACK
- 5) SLOTTED WALL STYLE IS RECOMMENDED FOR INSIDE EDGE OF PANEL CUT OUTS.
 SOLID WALL STYLE IS RECOMMENDED FOR STRAIGHT, OUTSIDE EDGES.
- 6) REELS MAY CONTAIN A MAXIMUM OF THREE SPLICES.
- 7) MAXIMUM USE TEMPERATURE 122° (50° C)



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
8	6/14/21	JBN	MDS	JADE	ADDED SLOTTED DIM. F & G FOR P/N GE_189F-C, CHANGED P/N TO GE_189F-C, REMOVED NOTE 8	102254
7	6/16/17	RVU	CLW	JHAC	ADD FRONT VIEW WITH ALL A, B, C, D, E, F, AND G DIMENSIONS TO MATCH WITH TABLE.	GAECN04200
6	02/16/15	BDK	MRJS	RGR0	F. ADDED NOTE #7 MAXIMUM TEMPERATURE RATING. G. GES189F-C WAS GE_189F-C AND ADDED NOTE 8.	GB0239FU

TITLE				ROLL FORM GROMMET EDGING	
CUSTOMER DRAWING					
ITEM REVISION NAME		G03597DM/03		PANDUIT	
DATASET FILE NAME		G03597DM_DC_GB0239FU_08/03A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:	
.X ± .XX ± THIRD ANGLE PROJECTION				SEE NOTE #2	
				DRAWING NUMBER:	
				GB0239FU	
DRAWN BY	DATE	CHK	SCALE	SIZE	
CEW	5-24-85		NONE	SHT 1 OF 1	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[GEE189F-A-C0](#) [GEE189F-A-C](#) [GEE189F-C](#) [GEE189F-C0](#)