





PART



CUTOUT

- NOTES:
1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
 2. DIMENSIONS IN [] ARE METRIC.
 3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 4. MATERIAL:
ENCLOSURE: POLYAMIDE 6
SEAL - NBR/EPDM
 5. PROTECTION CLASS WHEN USED WITH CEG GROMMETS:
NEMA 1,12
IP 65
 6. TEMPERATURE RANGE: -22 - 212 °F
 7. FLAMMABILITY: VO
 8. RoHS COMPLIANT
 9. COMPLIANCE: cURus
 10. WEIGHT: SEE TABLE

PART NUMBER	GL	D	S	INSTALLATION HEIGHT (EH)	SW1/SW2	NUMBER OF OPENINGS			THREAD METRIC	CUTOUT DIA. (d)	PART WEIGHT	PKG QTY
	in. (mm)	in. (mm)	in. (mm)			SMALL	MEDIUM	LARGE		in. (mm)	lbs. (g)	
CEST2-RL251	0.59 (15)	1.57 (40)	0.405 (10)	0.73 (18.5)	1.42/1.10 (36/28)	1	-	-	M25×1.5	1.00 (25.50)	0.053 (24.0)	5
CEST2-RL321	0.59 (15)	1.97 (50)	0.405 (10)	0.71 (18)	1.81/1.42 (46/36)	-	1	-	M32×1.5	1.28 (32.50)	0.062 (28.0)	5
CEST2-RL401	0.79 (20)	2.44 (62)	0.485 (12)	0.71 (18)	2.17/1.81 (55/46)	-	1	-	M40×1.5	1.59 (40.50)	0.116 (52.5)	5
CEST2-RL501	0.79 (20)	2.44 (62)	0.485 (12)	0.87 (22)	2.17/2.17 (55/55)	-	-	1	M50×1.5	1.99 (50.50)	0.134 (61.0)	5



00A	9/13/2022	SERH	MDS	JADE	INITIAL RELEASE	124032/00
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

PART NUMBER									
SEE TABLE									
TITLE									
CEST2-RL Control Drawing									
CUSTOMER DRAWING									
ITEM REVISION NAME									
00872EBG/00									
DATASET FILE NAME									
00872EBG_DC/00A									
								THIRD ANGLE PROJECTION	
MATERIAL								DRAWING NUMBER	
SEE NOTE 4								00872EBG - DC	
DRAWN BY	DATE	CHK	SCALE					SHEET 1 OF 1	
SERH	9/13/2022	MDS	1:1					B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[CEST2-RL321](#) [CEST2-RL501](#) [CEST2-RL401](#) [CEST2-RL251](#)