



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. MATERIAL: TPE LOW SMOKE, HALOGEN FREE
2. COLOR: BLACK
3. PART WEIGHT: 5.8 lbs PER 100 FT
4. 60±5 SHORE A DUROMETER RATING
5. TEMPERATURE RANGE OF -40°F (-40°C) TO 194°F (90°C)
6. BRACKETS [] DENOTES DIMENSIONS ARE IN MILLIMETERS AND ARE FOR REFERENCE ONLY

TITLE		MLTEH/SH CUSHION SLEEVING PCSLSH-B-CR										
		CUSTOMER DRAWING										
ITEM REVISION NAME		N41304BS/01										
DATASET FILE NAME		N41304BS_DC/01A										
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT										
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °												
01A 4/13 JAMB MIM RGRO UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO. ADDED TO NOTE #6: *AND ARE FOR REFERENCE ONLY		MATERIAL: SEE NOTES										
00A 12/11 JAMB ACC' --- DRAWING RELEASED		DRAWING NUMBER: N41304BS_DC										
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							JAMB	12/11	ACC	4:1		A



THIRD ANGLE
PROJECTION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PCSLSH-B-CR](#)