


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

1.44" [37] CT-2525CH, CT-2550CH & CT-2500CH (WITH LOCATOR)

1.25" [32] CT-2570CH (WITHOUT LOCATOR)



NOTES, UNLESS OTHERWISE SPECIFIED:

The CT-2500 and CT-2500/E Battery Operated Crimping Tools are designed to crimp #10 AWG thru #22 AWG Panduit terminals, disconnects and splices.

The CT-2500 and CT-2500/E Tools include:

- 1 – Battery Operated Crimping Tool (with battery cartridge)
- 1 – Spare Battery Cartridge
- 1 – Battery Charger
- 1 – Tool Case

| | |
|----------------------------|----------------------------------------------------------------------------|
| Weight (including battery) | 3.3 lbs. (1,5 kg) |
| Dimensions: | 11-3/4" L x 2-3/8" H x 3-1/8" W – with battery [298 L x 60 H x 80 W] mm |
| Crimping Time | 2 seconds |
| Crimping Force | 1.7 tons (15 kN) |

CT-2500 and CT-2500/E Battery Operated Crimping Tools are to be used with optional Crimping Heads: CT-2525CH, CT-2550CH and CT-2500CH, which are supplied with locator (for insulated); and CT-2570CH (for non-insulated), and are sold separately.

The CT-2500CH Crimping Head (frame only) is used with optional Crimping Die Inserts: CD-525, CD-550 and CD-570, which are sold separately.

The operation manual for the CT-2500 and CT-2500/E tools, plus optional crimping heads and die inserts can be found at: www.panduit.com.

Replacement Batteries and Battery Chargers are sold separately.

CT-2500BC Replacement Battery Cartridge

CT-2500CHR Replacement Battery Charger

CT-2500CHR/E Replacement Battery Charger for Europe

Dimensions in [brackets] are in millimeters.
All dimensions are for reference only.

F:\wrkgrp\rvusers\ENGR DOCS\CUSTOMER DRAWINGS\TP25386B01 04 CT-2500 CT-2500-E CD.doc

**CT-2500 TOOL BODY SHOWN WITH
CT-2525CH CRIMPING HEAD ATTACHED**

| | | | | | | | | | | | | | |
|-----|---------|-----|-------------|---------------------------------|------|-----|------------|-----|--|--------------------------------------------------------------------------------------------------------------------------------------------|--------------------|--------------------------------------------------------------------------------------------------|------------------|
| | | | | | | | | | | <div>PANDUIT</div> <div>CORP. TINLEY PARK, ILLINOIS</div> | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | CD*CT-2500 & CT-2500/E | | | |
| 04 | 4-07-14 | BLR | <i>BJPU</i> | UPD LOGO | 4734 | | <i>ABJ</i> | | | | | | |
| 03 | 1-27-14 | BLR | BJPU | UPD BRANDING | 4704 | | ABJ | | | UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.x) ± ---- (.xxx) ± ---- (.xx) ± ---- ANGLES ± ---- | | UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION. | |
| 02 | 4-04-08 | BLR | BJPU | ADD CT-2500CH & DIE INSERT INFO | 4290 | --- | JRWA | | | | | | |
| 01 | 8-01-07 | BLR | SRRE | UPD GRAPHIC W/LED | 4241 | --- | JRWA | | | DRAWN BY: BLR | MATL: ----- | SCALE NONE | |
| 00 | 3-02-07 | BLR | SRRE | RELEASED | 4241 | --- | SZ | | | DATE: 3-02-07 | | DRAWING NO. | DWG B SIZE |
| REV | DATE | BY | CHK'D | DESCRIPTION | ECN | - R | CUST | SUP | | CHK'D: SRRE | | TP25386B01 | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[CT-2500](#)