


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/100 PARTS (g)
	MIN. in (mm)	MAX. in (mm)											
UGCTE3S	1.0 (25.4)	3.0 (76.2)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	12.0 (305)	1.7 (43)	.6 (15)	50 (222)	STANDARD	.87 (396)
UGCTE5S	1.0 (25.4)	5.0 (127)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	18.7 (475)	1.7 (43)	.6 (15)	50 (222)	STANDARD	1.08 (490)

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
- 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS.

SS-27385.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY HOOK & LOOP CABLE TIES  
ULTRA-CINCH HOOK & LOOP TIES  
END MOUNT GROMMET

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± .25 (.XXX) ± .030  
(.XX) ± .125 ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

7	1/13/12	CR-MBA	DJW	ADDITIONAL MATERIAL ADDED; SPECIFIC COLOR REMOVED;		SS-27385	7	KLN			DRAWN BY JABO	MAT'L:  WOVEN HOOK/LOOP NYLON OR POLYESTER	SCALE NONE
6	4/12/06	FAB	DWW	ADDED WEIGHT TO DRAWING		27385	6	TGS			DATE 10/22/02		DRAWING NO. SS-27385
REV	DATE	BY	CHK	DESCRIPTION		ECN	R	CUST	SUP		CHK'D DWW		DWG A SIZE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[UGCTE5S-X6](#)