


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



CID\*\*-C, PHONE OR DATA ICON LOCATED HERE, IDENTIFIES INDIVIDUAL PORT. OPTIONAL, NOT SUPPLIED.

PANDUIT PART NO.	WEIGHT (APPOX.)
DP486X88TGY	2.2 lb (997.9 g)

- NOTES:
- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
  - MATERIAL:  
 PANEL HOUSING: STEEL  
 RJ45 MODULES: THERMOPLASTIC RESIN UL94V-0  
 PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0  
 BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B  
 RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
  - 48 PORT PATCH PANEL 8 POSITION 8 WIRE.
  - THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
  - FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) M6x1x15MM METRIC SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
  - DIMENSIONS IN BRACKETS ARE IN METRIC.
  - USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
  - RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.

MODEL FILENAME M02088AB_2RU_48PORT_PANEL_ASSY_03	SIZE A
DRAWING FILENAME M02479JA_DC237/00B	
TITLE DP6A 10GIG 48 PORT PATCH PANEL CUSTOMER DRAWING	
PANDUIT <sup>TM</sup> CORP. TINLEY PARK, ILL 60477	I.I. NUMBER
	PRODUCT SPEC
THIRD ANGLE PROJECTION	WORK INSTRUCTION
	SCALE .25 TO 1
DRAWN BY LZ	REVIEW DRAWING NUMBERS
DATE 3-4-06	PART NO. SEE CHART
CHK'D CEF	DRAWING NO. 02479-237

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	12-2-08	BJN	EJH	A. DP6A 10GIG WAS DP6 10GIG <sup>TM</sup>	02479-237				
R	3-4-06	LZ	CEF	RELEASED TO PRODUCTION	02479-237	CEF			CEF

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[DP486X88TGY](#)