



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WEIGHT
DPA24688TGY	1.26 lb (572.73 g)



- NOTES:
- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
 - MATERIAL:
 PANEL HOUSING: STEEL
 RJ45 MODULES: THERMOPLASTIC RESIN UL94V-0
 PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
 BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
 RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
 - 24 PORT ANGLED PATCH PANEL 8 POSITION 8 WIRE.
 - THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
 - FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) M6x1x15MM METRIC SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
 - DIMENSIONS IN BRACKETS ARE IN METRIC.
 - USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
 - RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.



CID**-C & CIP**-C, PHONE OR DATA ICON LOCATES HERE. IDENTIFIES INDIVIDUAL PORT. OPTIONAL, NOT SUPPLIED.

MODEL FILENAME	MO2088AC_1RU_24PORT_ANG_PANEL_ASSY_04	SIZE	A
DRAWING FILENAME	MO2479JD_DC240/00B		

DP6 PLUS 24 PORT ANGLED PATCH PANEL CUSTOMER DRAWING



I.I. NUMBER
PRODUCT SPEC

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
 DIMENSIONAL TOLERANCES ARE:
 (.X) ±.03 (.XXX) ±.005
 (.XX) ±.01 ANGLES ± 1°

WORK INSTRUCTION	
SCALE	.25 : 1

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	1-7-09	BJN	EJH	A. WAS 1070.48 g	02479-240				
R	3-4-06	LZ	CEF	RELEASED TO PRODUCTION	02479-240	CEF		CEF	CEF

DRAWN BY	LZ	REVIEW DRAWING NUMBERS
DATE	3-4-06	
CHK'D	CEF	

PART NO.	SEE CHART
DRAWING NO.	02479-240

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[DPA24688TGY](#)