



| | |
|---------------------|-----------------------------|
| PANDUIT PART NUMBER | WEIGHT |
| FRH45SC12 | 0.84 LB/EACH (383g/EACH) |

△ E NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 12x4 HORIZONTAL 45° ANGLE SPLIT COVER REQUIRES NO TOOLS FOR INSTALLATION AND/OR REMOVAL. THE SPLIT COVER CREATES A 3/4" (19.1) RADIUSED OPENING TO ALLOW FOR NEW CABLES TO BE ADDED WITHOUT THE NEED FOR REMOVING THE COVERS.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

ENG. REF.: D37617DN_DC_FRH45SC12_01.prt

CAD FILENAME/LAYERS **△ C** FRH45SC12.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
FIBERRUNNER 12x4 HORIZONTAL 45° ANGLE SPLIT COVER (FRH45SC12)
△ B CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ±
 (.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: JHNU
 DATE: 12-29-00
 CHK'D: HIW

MAT'L: ABS

SCALE: NONE
 DRAWING NO.: 37617-66
 DWG SIZE: A

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP | GMBH |
|-----|---------|-----|-----|--|----------|----|------|-----|------|
| - | ----- | --- | --- | E. REVISED GENERAL NOTES | ----- | -- | -- | | |
| - | ----- | --- | --- | D. REVISED PART WEIGHT C. REVISED CAD FILENAME | ----- | -- | -- | | |
| 1 | 6-29-06 | DTP | RN | B. REVISED DRAWING TITLE A. REVISED AND REDRAWN | 37617-66 | RN | RN | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FRH45SC12BL](#) [FRH45SC12OR](#)