


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITIES.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

DUPLEX FIBER OPTIC PATCH CORD
 FJ OPTI-PLUG TO LC CONFIGURATION
 CUSTOMER DRAWING



PANDUIT™
 CORP.
 TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES,
 UNLESS OTHERWISE SPECIFIED.
 DIMENSIONAL TOLERANCES ARE:
 (.X) (.XXX)
 (.XX) ANGLES

DRAWING FILENAME
 M02779BL_DC_00A.prt
 SCALE
 NONE

DRAWN BY
 MC
 DATE
 05-10-07
 CHK'D

MAT'L:

PART NO.
 SEE TABLE, SHT. 2
 DRAWING NO.
 02779-18
 (SHT. 1 of 2) SIZE
 A



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	06-04-07	MC		RELEASED TO PRODUCTION	02779-18				

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX FJ OPTI-PLUG TO LC FIBER OPTIC PATCH CORD

PANDUIT PART NO.	CABLE				FJ OPTI-PLUG			LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	COLOR	MAX. IL	MIN. RL	COLOR
FXE6P-10M*Y	RISER (OFNR)	10 GbE 50/125um OM3	DUPLEX 1.6mm Z1PCORD	AQUA	0.30dB	26dB	ELECTRIC IVORY	0.30dB	26dB	ELECTRIC IVORY
F5E6P-10M*Y		50/125um OM2		ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	ELECTRIC IVORY
F6E6P-10M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	ELECTRIC IVORY
F9E6P-10M*Y		9/125um OS1		YELLOW	0.75dB	55dB	BLUE	0.35dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

									DUPLEX FIBER OPTIC PATCH CORD FJ OPTI-PLUG TO LC CONFIGURATION CUSTOMER DRAWING					
									 PANDUIT TM CORP. TINLEY PARK, ILL 60477					
									 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.008 ANGLES		DRAWING FILENAME M02779BL_DC_00A.prt		
									DRAWN BY MC DATE 05-10-07 CHK'D		REVIEW DRAWING NUMBERS		SCALE NONE	
									RELEASED TO PRODUCTION ECN - R CUST SUP OTH		PART NO. SEE TABLE		DRAWING NO. 02779-18 (SHT. 2 of 2)	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	SIZE A				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[F5E6P-10M2Y](#) [F6E6P-10M2Y](#) [F9E6P-10M2Y](#)