



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

IDENTIFICATION LABEL

| CONTACT | CABLE WIRE COLOR |
|---------|------------------|
| 1       | WHITE/BLUE       |
| 2       | BLUE             |
| 3       | WHITE/ORANGE     |
| 4       | ORANGE           |



- NOTES: CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE PACKAGE QUANTITY.
1. GIGA-PUNCH CONNECTORS ON BOTH ENDS. THE PATCH CORDS CAN BE USED WITH GIGA-PUNCH CONNECTING BLOCKS.
  2. FEATURES INCLUDE A CLEAR CAP TO ENSURE PROPER WIRE SEQUENCE AND CONNECTOR ORIENTATION. RETAINING CLIP SECURE THE JACKET CLOSE TO THE POINT OF TERMINATION WHICH MINIMIZES WIRE UNTWISTING. INTEGRAL STRAIN RELIEF MINIMIZES STRESS ON WIRES DURING DISCONNECTION.
  3. TO CONNECTOR BLOCK.
  4. POLARIZED TO PREVENT REVERSE INSTALLATION TO CONNECTOR BLOCK.
  5. CATEGORY 5 UNSHIELDED TWISTED PAIR CABLE WITH 24AWG STRANDED TINNED COPPER CONDUCTOR.
  6. DIMENSIONS IN PARENTHESES ARE IN METRIC.

| PANDUIT P/N | MIN. CABLE LENGTH | WEIGHT                                |
|-------------|-------------------|---------------------------------------|
| GPPC21G3Y   | 3 FT.             | .998 LB/10 PCS<br>(452.69 g/10 PCS)   |
| GPPC21G5Y   | 5 FT.             | 1.505 LB/10 PCS<br>(682.66 g/10 PCS)  |
| GPPC21G7Y   | 7 FT.             | 1.856 LB/10 PCS<br>(841.87 g/10 PCS)  |
| GPPC21G9Y   | 9 FT.             | 2.125 LB/10 PCS<br>(963.88 g/10 PCS)  |
| GPPC21G14Y  | 14 FT.            | 3.029 LB/10 PCS<br>(1373.93 g/10 PCS) |
| GPPC21G20Y  | 20 FT.            | 3.866 LB/10 PCS<br>(1753.59 g/10 PCS) |
| GPPC21G1MY  | 1 METER           | 1.091 LB/10 PCS<br>(495.07 g/10 PCS)  |
| GPPC21G2MY  | 2 METER           | 2.183 LB/10 PCS<br>(990.14 g/10 PCS)  |
| GPPC21G3MY  | 3 METER           | 3.274 LB/10 PCS<br>(1485.20 g/10 PCS) |
| GPPC21G5MY  | 5 METER           | 5.457 LB/10 PCS<br>(2475.34 g/10 PCS) |

|   |         |                        |     |  |           |                       |      |     |     |
|---|---------|------------------------|-----|--|-----------|-----------------------|------|-----|-----|
| MODEL FILENAME  |         | DRAWING FILENAME       |     | TITLE  |           | SIZE                  |      |     |     |
|   |         | M02479LA_DC288_00B.PRT |     | 2 PAIR GIGA-PUNCH PATCHCORD<br>GPPC21GXXY CUSTOMER DRAWING |           | A                     |      |     |     |
| PANDUIT™<br>TINLEY PARK, ILL. 60477   |         | I.I. NUMBER            |     | PRODUCT SPEC   |           | WORK INSTRUCTION      |      |     |     |
| ALL DIMENSIONS UNLESS OTHERWISE SPECIFIED.<br>DIMENSIONAL TOLERANCES ARE:<br>(.XX) ±.031(.8) ANGLES ± |         | SCALE                  |     | NONE   |           | PART NO.              |      |     |     |
| DRAWN BY TA   |         | DATE 3-18-06           |     | SEE CHART  |           | DRAWING NO. 02479-288 |      |     |     |
| REV   | DATE    | BY                     | CHK | DESCRIPTION  | ECN       | R                     | CUST | SUP | OTH |
| R   | 3-18-06 | TA                     | MK  | RELEASED TO PRODUCTION                                     | 02479-288 |                       |      |     |     |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[GPPC2IG20Y](#) [GPPC2IG14Y](#) [GPPC2IG7Y](#) [GPPC2IG5Y](#) [GPPC2IG9Y](#) [GPPC2IG3Y](#)