



J-Mod® Cable Support System (continued)



JMjH2W-X20



JMjH2-X20



JMjCB-X



JMjCMB25-1-X



JMjCMB25-3-X



JMjDWB-1-X



JMjDWB-3-X



JMjTRB38-1-X



JMjTRB38-3-X



JMjSBCB87-1-X



JMjSBCB87-3-X

| Part Number | Part Description | Material* | Std. Pkg. Qty. | Std. Ctn. Qty. |
|---|---|-----------|----------------|----------------|
| J Hook with Maximum 2" Bundle Capacity | | | | |
| JMjH2W-X20 | J Hook for wall mount applications only. Two 1/4" (M6) mounting holes for user supplied screws. | Nylon 6.6 | 10 | 50 |
| JMjH2-X20 | J Hook with snap lock attachments for use with all brackets listed below. | Nylon 6.6 | 10 | 50 |

Chaining Bracket

| | | | | |
|---------|---|-------------------|----|----|
| JMjCB-X | Chaining bracket to extend J-Mod® capacity one level. Capacity: three levels maximum. For use with all single-level mounting brackets listed below. | Zinc Plated Steel | 10 | 50 |
|---------|---|-------------------|----|----|

Ceiling Mount Brackets

| | | | | |
|----------------|--|------------------|----|----|
| JMjCMB25-1-X | Single-level ceiling mount bracket with one 1/4" (M6) mounting hole. | Galvanized Steel | 10 | 50 |
| JMjCMB25-3-X** | Three-level ceiling mount bracket with one 1/4" (M6) mounting hole. Maximum capacity of six J Hooks. | Galvanized Steel | 10 | 50 |

Drop Wire Brackets

| | | | | |
|--------------|--|---|----|----|
| JMjDWB-1-X | Single-level drop wire bracket. Attaches to #12 wire or 3/8" (9.5mm) threaded rod. Maximum capacity of one J Hook per level. | Galvanized Steel with Metal Attachments | 10 | 50 |
| JMjDWB-3-X** | Three-level drop wire bracket. Attaches to #12 wire or 3/8" (9.5mm) threaded rod. Maximum capacity of one J Hook for each of three levels. Maximum static load of 40 pounds. | Galvanized Steel with Metal Attachments | 10 | 50 |

Threaded Rod Brackets

| | | | | |
|----------------|--|---|----|----|
| JMjTRB38-1-X | Single-level threaded rod bracket. Accepts 1/4" – 3/8" (6.4mm – 9.5mm) threaded rod. | Galvanized Steel with Metal Attachments | 10 | 50 |
| JMjTRB38-3-X** | Three-level threaded rod bracket. Accepts 1/4" – 3/8" (6.4mm – 9.5mm) threaded rod. Maximum capacity of six J Hooks. | Galvanized Steel with Metal Attachments | 10 | 50 |

Screw-On Beam Clamp Brackets

| | | | | |
|-----------------|--|---|----|----|
| JMjSBCB87-1-X | Single-level screw-on beam clamp bracket for use with flanges up to 3/4" (19.1mm) thick. | Galvanized Steel with Metal Attachments | 10 | 50 |
| JMjSBCB87-3-X** | Three-level screw-on beam clamp bracket for use with flanges up to 3/4" (19.1mm) thick. Maximum capacity of six J Hooks. | Galvanized Steel with Metal Attachments | 10 | 50 |

*Suitable for use in air handling spaces and listed in accordance with UL 2043 and CAN/ULC S102.2 when mounted as single units or in pairs. Maximum spacing of 4' (1220mm) required between mount points. (Flame Spread Rating = 0, Smoke Developed Classification = 30).

**Not for use with chaining brackets.

| | Maximum Cable Capacity | | |
|-----------------|------------------------|----------------|-----------------|
| | Cat 6A (0.300") | Cat 6 (0.240") | Cat 5e (0.225") |
| JMjH2W or JMjH2 | 30 | 46 | 55 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[JMSBCB87-1-X](#)