

Search within category

BUY NOW

DESIGN / INSTALL



S4-38R-T

Tubular Ring Terminal, 4 AWG, 3/8" stud size, non-insulated, bulk package.

Specs	Packaging Details	Tools	Documents	★ Add to Favorites	🛒 Add to BOM
Product Type	Loose Piece Ring Terminal				
Stud Size	3/8"				
Wire Range	4 AWG				
Wire Range (mm²)	25				
Barrel Configuration	Beveled				
Barrel Type	Seamless Tubular				
Base Material	Copper				
Insulation	Non-Insulated				
Panduit Color Code	Metallic				
Plating Type	Tinned				
Part Number Series	S				
Clearance	—				
Clearance (mm)	—				
Length (In.)	1.5				
Length (mm)	38.1				
Stock	0.07				
Stock (mm)	1.778				
Width (In.)	0.62				
Width (mm)	15.748				
Wire Strip Length (In.)	1/2" (0.50)				
Wire Strip Length (mm)	12.7				
Flammability Rating	—				
Max. Voltage Rating	UL-CSA Voltage Rating 35KV				
Temperature Rating	UL-CSA Temperature Rating 90 Degrees Celsius				
CA-800/EZ Series Crimp Die	—				
CA9 Series Crimp Die	—				
Tool	CT-1700,CT-720,CT-930,CT-930CH,CT-940CH,CT-2001,CT-2002,CT-980,CT-2980,CT-980CH				

Stud Hole Size (In.)	3/8"
Tongue Width (In.)	0.62
Barrel Length (In.)	0.48
Barrel O.D.	0.38
CSA Certified	C22.2 No. 65
Mil. Std. Part Number	—
UL Listed	UL486A-486B
Packaging Type	Box
Angle	Straight
Barrel I.D.	0.28
Part Features	• Seamless tubular barrel provides a consistent high performance quality crimp • Round double thick tongue for reliable power applications • Barrel of terminal internally beveled to provide quick and easy wire insertion • Inspection window allows visual inspection of proper wire insertion
Tongue Thickness	0.07
RoHS Compliancy Status	Compliant
Min. Order Qty.	200.0000

[Back to Top](#)[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S4-38R-T](#)