



Search within category

GO

BUY NOW

DESIGN / INSTALL



F9URPEN54ANF074

OS2 24-fiber, Interconnect, Plenum, 24F MPO Female to (2) 12-fiber Female PanMPO, Method A, Std IL, 74 Feet, Yellow.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Application	Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure.
Assembly Length Range	20-29 m (66-98 ft)
Cable Color	Yellow
Connector 1 Type	24F MPO
Connector 2 Type	(2)12F MPO
Fiber Type	OS2
Flammability Rating	Plenum (OFNP)
Length (ft.)	74.00
Length (m)	22.56
Standards	TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[F9URPEN54ANF074](#)