




Search within category

GO

BUY NOW

DESIGN / INSTALL



F9URLENENANM001

OS2 24-fiber, Interconnect, LSZH, 24F MPO Female to 24F MPO Female, Method A, Std IL, 1 m, Yellow.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Application	Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure.
Assembly Length Range	0-9 m (0-32 ft)
Cable Color	Yellow
Connector 1 Type	24F MPO
Connector 2 Type	24F MPO
Fiber Count	24
Fiber Type	OS2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Length (ft.)	3.28
Length (m)	1.0
Standards	TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[F9URLENENANM001](#)