



Search within category

GO

BUY NOW

DESIGN / INSTALL



**FXURLENENXNM017**

OM3 24-fiber, Interconnect, LSZH, 24F MPO Female to 24F MPO Female, Method A, Optimized IL, 17 m, Aqua.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

|                        |   |
|------------------------|---|
| Application            | Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure. |
| Assembly Length Range  | 10-19 m (33-65 ft)  |
| Cable Color            | Aqua  |
| Connector 1 Type       | 24F MPO   |
| Connector 2 Type       | 24F MPO   |
| Fiber Count            | 24  |
| Fiber Type             | OM3   |
| Flammability Rating    | Low Smoke Zero Halogen (LSZH)   |
| Length (ft.)           | 55.76   |
| Length (m)             | 17.00   |
| Standards              | TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant  |
| RoHS Compliancy Status | Compliant   |
| Min. Order Qty.        | 1.0000  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FXURLENENXNM017](#)