



Search within category GO

BUY NOW

DESIGN / INSTALL



FXURPEN74XNF064

OM3 24-fiber, Interconnect, Plenum, 24F MPO Female to (2) 12-fiber Female PanMPO, Method A, Optimized IL, 64 Feet, Aqua.

Specs Packaging Details Documents

★ Add to Favorites Add to BOM

Application	Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure.
Assembly Length Range	10-19 m (33-65 ft)
Cable Color	Aqua
Connector 1 Type	24F MPO
Connector 2 Type	(2)12F MPO
Fiber Cable Type	Multi mode 50/125
Fiber Type	OM3
Flammability Rating	Plenum (OFNP)
Length (ft.)	64
Length (m)	19.51
Standards	TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FXURPEN74XNF064](#)