



Search within category GO

BUY NOW

DESIGN / INSTALL



FZURPEN74XNF012

OM4 24-fiber, Interconnect, Plenum, 24F MPO Female to (2) 12-fiber Female PanMPO, Method A, Optimized IL, 12 Feet, Aqua.

Specs Packaging Details Documents

★ Add to Favorites Add to BOM

| | |
|------------------------|---|
| Application | Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure. |
| Assembly Length Range | 0-9 m (0-32 ft) |
| Cable Color | Aqua |
| Connector 1 Type | 24F MPO |
| Connector 2 Type | (2)12F MPO |
| Fiber Count | 24 |
| Fiber Type | OM4 |
| Flammability Rating | Plenum (OFNP) |
| Length (ft.) | 12 |
| Length (m) | 3.66 |
| Standards | TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant |
| RoHS Compliancy Status | Compliant |
| Min. Order Qty. | 1.0000 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[FZURPEN74XNF012](#)