



Search within category

GO

BUY NOW

DESIGN / INSTALL



FZURPEN74XNF024

OM4 24-fiber, Interconnect, Plenum, 24F MPO Female to (2) 12-fiber Female PanMPO, Method A, Optimized IL, 24 Feet, Aqua.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

|                        |                                                                                                                                           |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|
| Application            | Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure. |
| Assembly Length Range  | 0-9 m (0-32 ft)                                                                                                                           |
| Cable Color            | Aqua                                                                                                                                      |
| Connector 1 Type       | 24F MPO                                                                                                                                   |
| Connector 2 Type       | (2)12F MPO                                                                                                                                |
| Fiber Count            | 24                                                                                                                                        |
| Fiber Type             | OM4                                                                                                                                       |
| Flammability Rating    | Plenum (OFNP)                                                                                                                             |
| Length (ft.)           | 24                                                                                                                                        |
| Length (m)             | 7.32                                                                                                                                      |
| Standards              | TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant                                                        |
| RoHS Compliancy Status | Compliant                                                                                                                                 |
| Min. Order Qty.        | 1.0000                                                                                                                                    |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FZURPEN74XNF024](#)