







THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT JACKETED FIBER PATCH
CORD MASTER OPTIONS LIST



1st POSITION - FIBER PRODUCT

F - FIBER

2nd POSITION - FIBER TYPE

9 - SINGLEMODE
S - SIG-CORE (OM4+)
X - OM3
Z - OM4

3rd POSITION - FIBER COUNT

2 - 2 FIBER

4th POSITION - CABLE TYPE

E - 1.6mm DUPLEX
3 - 3mm DUPLEX (SC-SC ONLY)

5th POSITION - JACKET TYPE

P - PLENUM
R - RISER
L - LSZH

6th POSITIONS - CONNECTOR (END A)

Q - PUSH PULL DUPLEX LC
L - LC DUPLEX
S - SC DUPLEX

7th POSITIONS - CONNECTOR VARIANT

1 - PUSH PULL DUPLEX LC
N - NO VARIANT

8th POSITION - CONNECTOR (END B)

Q - PUSH PULL DUPLEX LC
L - LC DUPLEX
S - SC DUPLEX

9th POSITIONS - CONNECTOR VARIANT

1 - PUSH PULL DUPLEX LC
N - NO VARIANT

10th POSITION - PERFORMANCE/POLARITY

S - STANDARD IL
T - STANDARD IL PAIR FLIPPED
O - OPTIMIZED IL
P - OPTIMIZED IL PAIR FLIPPED
N - ULTRA LOW IL (OM4 & OM4+ ONLY)

11th POSITION - PULLING EYE


N - NO PULLING EYE

12th POSITION - UNIT OF MEASURE

F - FEET
M - METERS

13th, 14th, AND 15th POSITIONS - ASSEMBLY LENGTH

F - 001-050 FEET
M - 001-050 METERS

							TITLE JACKETED DUPLEX FIBER PATCH CORDS CUSTOMER DRAWING					
							ITEM REVISION NAME M02779DX/00					
							DATASET FILE NAME M02779DX_DC/00B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.762] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 1 °			MATERIAL :		
01	07-06-16	SAT	RWB	MMN	SEE SHEET 1 FOR REVISION HISTORY.	M02779DX-DC	 THIRD ANGLE PROJECTION			DRAWING NUMBER: M02779DX - DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 01-04-16	CHK RWB	SCALE NONE	SHT 2 OF 2	SIZE B



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

FZ23RSNSNONF005	FZ23RSNSNSNF003	FZ2ERLNSNSNF015	FX23RSNSNONF013	FZ2ELQ1SNSNM035
FZ23RSNSNONM045	FZ2ERLNSNONF012	FZ23LSNSNONM008	FZ23RSNSNONM013	FZ2ERQ1SNSNM007
FX2ERQ1SNSNF009	FZ23RSNSNONF019	FX23LSNSNONM016	FX2ERQ1SNSNF026	FX23RSNSNONM007
FZ23RSNSNONF022	FX23RSNSNONM004	FZ2ELQ1SNONM047	FZ2ERQ1SNSNF017	FX23LSNSNONM014
FX23RSNSNSNF040	FX23RSNSNONM025	FZ2ELQ1SNONM030	FX23RSNSNONF011	FZ23RSNSNONF006
FZ2ERQ1SNSNM008	FZ2ERLNLNONF011	FX2ERQ1SNSNF010	FZ2ELQ1SNSNM004	FZ23LSNSNONM023
FX23LSNSNONM048	FX23RSNSNSNF001	FX2ERQ1SNSNF024	FZ2ERQ1SNSNM025	FZ2ELQ1SNSNM002
FX23LSNSNONM032	FX2ERQ1SNSNF090	FZ23LSNSNONM021	FZ23RSNSNONM012	FZ2ERLNSNSNF016
FZ23LSNSNONM041	FZ2ELQ1SNSNM019	FX23RSNSNSNF019	FX23RSNSNONF014	FX2ERLNLNSNF018
FZ2ERLNSNONF013	FZ2ERQ1SNONF001	FX23RSNSNSNF016	FZ2ERLNSNSNF013	FZ23RSNSNONM029
FZ23RSNSNONM046	FZ2ERQ1SNSNM040	FZ23LSNSNONM038	FZ2ELQ1SNONM013	FZ2ERQ1SNONM042
FZ23RSNSNONM043	FZ2ERLNSNONF010	FX23RSNSNSNF050	FX23RSNSNONM038	FX23LSNSNONM030
FZ2ERLNSNONF011	FZ2ERQ1SNONM023	FZ2ERQ1SNONM006	FZ2ERQ1SNONM040	FZ23RSNSNSNF002
FZ2ELQ1SNONM048	FZ2ERLNLNONF012	FZ2ERQ1SNSNF015	FX23RSNSNONM005	FZ2ERQ1SNONF016
FZ23RSNSNONF004	FX2ERQ1SNSNF008	FX23RSNSNSNF045	FZ23LSNSNONM040	FX23RSNSNONM042
FZ2ERQ1SNONF004	FZ2ERQ1SNONM022	FZ2ELQ1SNSNM021	FZ2ERQ1SNONM024	FZ23RSNSNONF021
FZ2ERQ1SNONM025	FX23LSNSNONM049	FX23RSNSNSNF002	FX2ERQ1SNSNF025	FZ2ELQ1SNONM045
FZ2ERQ1SNONM008	FX23RSNSNONM023	FX23RSNSNONM040	FZ2ERQ1SNSNM023	FZ2ELQ1SNSNM005
FZ2ERQ1SNSNM006	FZ23LSNSNONM024	FZ23RSNSNSNF019	FZ23LSNSNONM007	FZ2ERLNLNONF009
FZ2ELQ1SNSNM036	FZ2ERQ1SNSNF012	FZ2ERQ1SNONM019	FZ23RSNSNSNF001	FZ2ERQ1SNSNM043