

## Cable connector - HC-26S1N8A80AW - 1623294

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable connector, straight, Screw locking, M27, number of positions: 26, type of contact: Socket, shielded: yes, cable diameter range: 13.5 mm ... 14.5 mm



### Key Commercial Data

Packing unit	12 pc
GTIN	
GTIN	4055626273228

### Technical data

#### General

Note	Order information: Order crimp contacts Ø 1 mm separately
Type of locking	Screw locking
Direction of rotation of contact chamber numbering	Standard
Coding	N
Type of contacts	Socket
Number of positions	26
Contact diameter of power contacts	1 mm
Nominal current per power contact at 25°C	8 A
Conductor entry	13.5 mm ... 14.5 mm
Pg housing screw connection	none

#### Ambient conditions

Degree of protection	IP67, when plugged in
----------------------	-----------------------

#### Specifications according to DIN EN 61984:2001

Installation height max.	2000 m
Nominal / operating voltage of power contacts	150 V
Rated surge voltage of power contacts	1.5 kV
Overvoltage category of power contacts	II

# Cable connector - HC-26S1N8A80AW - 1623294

## Technical data

Specifications according to DIN EN 61984:2001


Degree of pollution of power contacts	3
---------------------------------------	---

## Environmental Product Compliance


REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Schematic diagram



Dimensional drawing



Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1623294](#)