


Plug - FK-MPT 0,5/ 6-ST-3,5 BD:V-B - 1701577

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


PCB connector, nominal current: 4 A, number of positions: 6, pitch: 3.5 mm, connection method: Push-in spring connection, color: green, contact surface: Tin




The figure shows a 10-position version of the product

Your advantages

- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- Intuitive use through colour coded actuation lever
- Potentials can be easily looped through – ideal for BUS applications
- Small component size for applications where space is at a premium



Key Commercial Data

Packing unit	50 pc
GTIN	 4 046356 544894
GTIN	4046356544894

Technical data

Dimensions

Length [l]	9.5 mm
Width [w]	21.5 mm
Height [h]	8.5 mm
Pitch	3.5 mm
Dimension a	17.5 mm

General

Range of articles	FK-MPT 0,5/...-ST
Number of positions	6
Connection method	Push-in spring connection
Rated voltage (III/3)	160 V

Plug - FK-MPT 0,5/ 6-ST-3,5 BD:V-B - 1701577

Technical data

General

Connection in acc. with standard	EN-VDE
Nominal current I _N	4 A
Nominal cross section	0.5 mm ²

Connection data

Conductor cross section solid min.	0.12 mm ²
Conductor cross section solid max.	0.5 mm ²
Conductor cross section AWG min.	26
Conductor cross section AWG max.	20
Minimum AWG according to UL/CUL	28
Maximum AWG according to UL/CUL	20

Standards and Regulations

Connection in acc. with standard	EN-VDE
	CUL

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals


Approvals

Approvals

UL Recognized / cUL Recognized / SEV / EAC / cULus Recognized


Ex Approvals

Approval details


UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
	D	B	
Nominal voltage U _N	300 V	300 V	
Nominal current I _N	4 A	4 A	
mm ² /AWG/kcmil	28-20	28-20	

Plug - FK-MPT 0,5/ 6-ST-3,5 BD:V-B - 1701577

Approvals

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
----------------	---	---	--------------

	D	B
Nominal voltage UN	300 V	300 V
Nominal current IN	4 A	4 A
mm ² /AWG/kcmil	28-20	28-20

SEV		https://www.electrosuisse.ch/de/meta/shop/produktezertifikate.html	IK-3558-M2
-----	---	---	------------

Nominal voltage UN	160 V
Nominal current IN	4 A
mm ² /AWG/kcmil	0.5

EAC		B.01742
-----	---	---------

cULus Recognized	
------------------	---

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1701577](#)