

Single PCB terminal block - ZFK4DSA 1,5-5,08-24 BD:O8-I1 Q - 1711274

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




PCB terminal block, nominal current: 12 A, nom. voltage: 400 V, pitch: 5.08 mm, number of positions: 24, connection method: Spring-cage connection, mounting: Wave soldering, color: green. The article can be aligned to create different nos. of positions!

The figure shows an 10-position version

Your advantages

- ✓ Defined contact force ensures that contact remains stable over the long term
- ✓ Clamping space opened by means of fixed screwdriver enables convenient conductor connection
- ✓ Conductor connection on several levels enables higher contact density
- ✓ The latching on the side enables various numbers of positions to be combined



Key Commercial Data

Packing unit	10 pc
GTIN	
GTIN	4055626230948

Technical data

Dimensions

Length [L]	42.4 mm
Pitch	5.08 mm
Height	48 mm
Solder pin [P]	3.4 mm
Hole diameter	1.3 mm

General

Range of articles	ZFK4DS(A) 1,5
Insulating material group	I
Rated voltage (III/2)	400 V
Nominal current I _N	12 A

Single PCB terminal block - ZFK4DSA 1,5-5,08-24 BD:O8-I1 Q - 1711274

Technical data

General

Nominal cross section	1.5 mm ²
Flammability rating according to UL 94	V0
Number of positions	24

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1711274](#)