


Cable - CABLE FLK50/EZ-DR/ 100/SC047 - 2902863

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (1x 50-position); cable length: 10 m



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	20 pc
GTIN	 4 046356 912723
GTIN	4046356912723

Technical data

General

Nominal voltage U_N	≤ 24 V DC
Max. current carrying capacity per path	0.5 A
Length of cable	10 m

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Connector 1

Connection name	Flat-ribbon cable connector
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	50

Connector 2

Connection name	Flat-ribbon cable connector
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	50

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
------------	--

Cable - CABLE FLK50/EZ-DR/ 100/SC047 - 2902863

Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2902863](#)