

Conductor marker carrier - PATO 1/18 - 0823740

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker carrier, transparent, unlabeled, mounting type: clip on, cable diameter range: 2 ... 3.5 mm, lettering field size: 4 x 18 mm

Your advantages

- Can be labeled using UC-WMT ... and US-WMT ... plastic labels or EMT insert strips
- These marking collars are used for subsequent labeling of systems that have already been wired

Key Commercial Data

| | |
|------------------------|---------------|
| Packing unit | 500 pc |
| Minimum order quantity | 500 pc |
| GTIN | |
| GTIN | 4046356333658 |

Technical data

Dimensions

| | |
|----------------|-----------------|
| Length (b) | 18 mm |
| Width (a) | 5.6 mm |
| Cable diameter | 2 mm ... 3.5 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -50 °C ... 80 °C |
|---------------------------------|------------------|

General

| | |
|--|---------------|
| Color | transparent |
| Type | Profile |
| Components | Silicone-free |
| Flammability rating according to UL 94 | V0 |
| Material | PVC |
| Marking mounting type | clip on |

Conductor marker carrier - PATO 1/18 - 0823740

Technical data

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27400401 |
| eCl@ss 4.0 | 27061700 |
| eCl@ss 4.1 | 27061700 |
| eCl@ss 5.0 | 27400400 |
| eCl@ss 5.1 | 27400400 |
| eCl@ss 6.0 | 27149100 |
| eCl@ss 7.0 | 27149153 |
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC002248 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0823740](#)