

## Replacement die - CRIMPFOX-M TC 4/DIE - 1212075

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die, for Crimpfox-M, for turned contacts 0.5 ... 4 mm<sup>2</sup>, packed in a serial storage box

### Your advantages

- Marked die stations for precise processing of corresponding cross sections
- For CK 2,5 ED..., CK 4,0 ED... turned pin and socket contacts

### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356452540

### Technical data

#### Dimensions

Length (b)	114 mm
Width (a)	75 mm
Height (c)	25.5 mm

#### General

Color	black
Compression	Square crimp
Type of contact	Turned contacts
Designation	Crimping position 1
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
AWG min	20
AWG max	18
Designation	Crimping position 2
Max. cross section	1.5 mm <sup>2</sup>
AWG max	16
Designation	Crimping position 3
Max. cross section	2.5 mm <sup>2</sup>

# Replacement die - CRIMPFOX-M TC 4/DIE - 1212075

## Technical data

### General

AWG max	14
Die station	Crimping position 4
Max. cross section	4 mm <sup>2</sup>
AWG max	12
Weight	72 g
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	4 mm <sup>2</sup>
AWG min	20
AWG max	12

## Classifications

### eCl@ss

eCl@ss 10.0.1	21019290
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21019290

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 19.0	27111518

## Approvals

### Approvals

## Replacement die - CRIMPFOX-M TC 4/DIE - 1212075

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212075](#)