

## Replacement die - CRIMPFOX-M 50/DIE - 1212082

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die, for Crimpfox-M, for ferrules 35 - 50 mm<sup>2</sup>, packed in a serial storage box

### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356454520

### Technical data

#### Dimensions

Length (b)	114 mm
Width (a)	75 mm
Height (c)	25.5 mm

#### General

Color	black
Compression	Trapezoidal crimp
Type of contact	Ferrules
Designation	Crimping position 1
Max. cross section	35 mm <sup>2</sup>
AWG max	2
Designation	Crimping position 2
Max. cross section	50 mm <sup>2</sup>
AWG max	0
Weight	86 g
Min. cross section	35 mm <sup>2</sup>
Max. cross section	50 mm <sup>2</sup>

### Classifications

eCl@ss

eCl@ss 10.0.1	21019290
---------------	----------

# Replacement die - CRIMPFOX-M 50/DIE - 1212082

## Classifications

### eCl@ss

eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21019290

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 19.0	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212082](#)