


## Replacement die - CRIMPFOX-C50 R35-50/DIE - 1212350

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



pre-round die (pair), for CRIMPFOX-C50, for sector cable 35 + 50 mm<sup>2</sup>

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 455060
GTIN	4046356455060

### Technical data

#### General

Color	black
Compression	Oval crimp
Min. cross section	35 mm <sup>2</sup>
Max. cross section	50 mm <sup>2</sup>
AWG min	2
AWG max	1/0
Min. cross section	35 mm <sup>2</sup>
Max. cross section	50 mm <sup>2</sup>

### Classifications

#### eCl@ss

eCl@ss 10.0.1	21019290
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21019290

# Replacement die - CRIMPFOX-C50 R35-50/DIE - 1212350

## Classifications

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 19.0	27111518

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212350](#)