

## Tool bag, equipped - TOOL-BAG - 1212504

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Toolbag, with laptop and document compartment, equipped with: cable cutter, diagonal cutter, stripping pliers, insulation stripper, crimp tool set, Combination, needle-nose, and water pump pliers, VDE screwdriver bladed: 0.4x2.5/0.5x3.0/1.0x4.0/1.0x5.5 crosshead: PHO/PH1/PH2 Control cabinet key, voltage tester, ferrule box Blades, tape measure, toolbag

### Your advantages

- Rugged and heavy-duty tool bags
- Universal tool sets, with cutting, stripping, crimping, and testing tools from the TOOL fox tool range

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 528405
GTIN	4046356528405

### Technical data

#### Dimensions

Length (b)	410 mm
Width (a)	225 mm
Depth	225 mm
Height (c)	340 mm

#### General

Weight	1.73 kg
--------	---------

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Articles in set

#### Cable-cutting tool - CUTFOX 25 VDE - 1212127



Cable cutter, precision blade with macro-notching, for copper and aluminum up to 70 mm<sup>2</sup>, VDE 1000 V AC/1500 V DC tested

## Tool bag, equipped - TOOL-BAG - 1212504

### Articles in set

---

#### Diagonal cutter - CUTFOX-S VDE - 1212207



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested

---

#### Stripping tool - WIREFOX 10 - 1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

---

#### Stripping tool - WIREFOX-D 40 - 1212161



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

---

#### Crimping pliers set - CRIMPFOX-M SET - 1212093



Crimping pliers set, consisting of CRIMPFOX-M (pliers) and dies for insulated cable lugs 0.5 ... 2.5 mm<sup>2</sup> (1212074), non-insulated conduit lugs 0.5 ... 6 mm<sup>2</sup> (1212079) and ferrules 0.25 ... 10 mm<sup>2</sup> (1212080) and 16/25 mm<sup>2</sup> (1212081).

---

#### Tool - UNIFOX-C VDE - 1212202



Combination pliers, notched gripping surface, VDE 1000 V AC/1500 V DC tested, size: 180 mm

---

## Tool bag, equipped - TOOL-BAG - 1212504

### Articles in set

Tool - UNIFOX-P VDE - 1212204



Needle-nose pliers with blade, notched grip area, VDE 1000 V AC/1500 V DC tested

---

Tool - UNIFOX-WP - 1212365



Water pump pliers, with groove joint, grip areas with dual notching, acc. to VDE ISO 8976

---

Screwdriver - SZS 0,4X2,5 VDE - 1205037



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZS 0,5X3,0 VDE - 1207404



Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZS 1,0X4,0 VDE - 1205066



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

---

## Tool bag, equipped - TOOL-BAG - 1212504

### Articles in set

Screwdriver - SZS 1,0X6,5 VDE - 1205079



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZK PH0 VDE - 1205147



Screwdriver, PH crosshead, VDE insulated, size: PH 0 x 80 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZK PH1 VDE - 1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZK PH2 VDE - 1205163



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

---

Voltage tester - DUSPOL EXPERT - 1209091



Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1000 V DC, IP65

---

## Tool bag, equipped - TOOL-BAG - 1212504

### Articles in set

Control cabinet key - USS 4 - 1203149



Control cabinet key, metal, for all common types of control cabinet

Range box - AI SORTI BOX RD - 3202960



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

Tool bag, unequipped - TOOL-BAG EMPTY - 1212500



Tool bag, with document and laptop compartments, unequipped

Measuring instrument - MEASURING TAPE 5M I/M - 1200304



Measuring tape with automatic tape feed and locking mechanism, measuring rail: imperial/metric, length: 5 m

## Classifications

eCl@ss

eCl@ss 10.0.1	21045003
eCl@ss 4.0	21043000
eCl@ss 4.1	21043000
eCl@ss 5.0	21049000
eCl@ss 5.1	21049000
eCl@ss 6.0	21049000
eCl@ss 7.0	21045003
eCl@ss 8.0	21045003
eCl@ss 9.0	21045003

# Tool bag, equipped - TOOL-BAG - 1212504

## Classifications

### ETIM

ETIM 3.0	EC000149
ETIM 4.0	EC000149
ETIM 5.0	EC000149
ETIM 6.0	EC000149
ETIM 7.0	EC000149

### UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121410
UNSPSC 13.2	27113201
UNSPSC 18.0	27113201
UNSPSC 19.0	27113201
UNSPSC 20.0	27113201
UNSPSC 21.0	27113201

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01750
-----	---	--------------------------

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212504](#)